


MedArt

Smoke Evacuation unit





CompairS

Details of Exhaust- and Filtration unit CompairS

| Description | Unit | Details |
|---|-------------------|-------------|
| Air flow | m ³ /h | 220 |
| Effective air flow | m ³ /h | 30-150 |
| Max. static pressure | Pa | 13000 |
| Voltage | V | 230 |
| Frequency | Hz | 50-60 |
| Motor power | kW | 1,2 |
| Protection class | - | 1 |
| Motor and drive system | - | brush motor |
| noise level | db(A) | approx. 50 |
| noise level with noise reduction module | db(A) | n/A |
| Serial interface | - | None |
| Weight | Kg | ca. 27 |
| Dimensions(HxWxD) | mm | 560x290x290 |
| Intake socket (N/D) | | |
| Intake socket (N/D) 12 | quantity | n/A |
| Intake socket (N/D) 32 | quantity | n/A |
| Intake socket (N/D) 50 | quantity | 2 |
| Intake socket (N/D) 63 | quantity | n/A |
| Intake socket (N/D) 80 | quantity | n/A |
| Intake socket (N/D) 100 | quantity | n/A |
| Intake socket (N/D) 125 | quantity | n/A |
| Intake socket (N/D) 160 | quantity | n/A |
| Intake socket (N/D) 180 | quantity | n/A |
| Intake socket (N/D) 200 | quantity | n/A |
| Intake socket (N/D) 250 | quantity | n/A |
| Filter Configuration | | |
| Al-filter(G3) | n/A | |
| Pre-filter (F5) | included | |
| Bag filter (F5) | n/A | |
| Z-Line filter (F6/F7) | n/A | |
| Particle filter (H13) | included | |
| MP-Tec | n/A | |
| Cartridge filter | n/A | |
| Atticated carbon/BAC granulate | 7l / 3,5kg | |

Containing:

- initial filter equipment
- filter control
- hour-meter
- integrated speed regulator
- 4 caster for moving

Incl:

Exhaust arm, white, Ø50, L=850 mm, designed for mounting on top of the filtration equipment.
Extractor tube 50mm, L=210mm

Article No.:

TBH-12524 (main unit)
TBH-11442 (foot switch)

MedArt A/S

(Asah Medico A/S)
Valseholmen 11-13
DK-2650 Hvidovre
Denmark

Tel +45 3634 2300
Fax +34 3634 2323
info@medart.dk
www.medart.dk

MedArt Corporation

1479 Clencrest Drive
Suite A
San Marcos, CA 92078
USA

Tel +1 760 798 2740
Fax +1 760 798 2750
info@medart-corp.com
www.medart-corp.com

MedArt (Deutschland) GmbH

Rudendorfer Weg 39
D-96188 Stettfeld
Germany

Tel +49 09522 / 707 222
Fax +49 09522 / 707 210
medart-laser@medart.dk
www.medart.dk